

Euromex illumination station


LE.5212

HIGHLIGHTS

- Professional base station with various LED cold light sources
- For Materials Science and Stereo microscopy
- Four independent and autonomous illuminators
- Complete illumination solution in one station
- Available with white light spectrum and three monochromatic wavelengths

TECHNICAL SPECIFICATIONS

- Light source station with multiple power supply connections for two self-sustaining gooseneck-type guides, one ring light and one transmitted stage illumination
- Each power supply connection controls the LED intensity independently from the other power supply connections
- Oblique illumination with two self-sustaining Gooseneck-type LED light guides equipped with either a 3 Watt white 6500 K LED or a 365 nm UV-LED or a 395 nm or 420 nm Violet-LED
- Each self-sustaining Gooseneck-type LED guide is equipped with a 3-lens focusing head and has a length of 56 cm
- Homogeneous conical beam of light illumination with a white 6.500 K LED ring light generating with 60 LEDs up to 24.000 Lux. Mounting diameters from 21 to 61 mm
- Transmitted light stage illumination with a 6.500 K white LED generating up to 8.000 Lux with 42 LEDs. Stage diameter 94.5 and 15 mm thick
- Station to be placed on a tabletop as standalone illumination unit or mounted on the pole of a stereo microscope with diameters up to 44 mm or with 35- and 25-mm pole mounting adapter rings
- Operating voltage: 100-240VAC/50-60Hz— 5VDC/4A
- Dimensions (main body): (h) 40 x (w) 65 x (d) 200 mm
- Weight: 1.9 kg



MODELS	3 W Gooseneck guide LED	4 W white LED ring light	2 W white LED transmitted light stage
LE.5212	White LED, 6.500 K	•	•
LE.5212-365	365 nm, monochrome	•	•
LE.5212-395	395 nm, monochrome	•	•
LE.5212-420	420 nm, monochrome	•	•



WARNING:

For your own safety it is highly recommended to wear protective orange glasses when using the 365 nm gooseneck

ACCESSORIES AND SPARE PARTS

- LE.5260** Interchangeable self-sustaining gooseneck-type guide with a white 6.500 K high-power LED for NZ.9018, LE.5207 or LE.5212, 1 pc (A)
- LE.5261** Interchangeable self-sustaining gooseneck-type guide with a 365 nm high-power UV-LED for NZ.9018, LE.5207 or LE.5212, 1 pc (B)
- LE.5262** Interchangeable self-sustaining gooseneck-type guide with a 395 nm high-power Violet-LED for NZ.9018, LE.5207 or LE.5212, 1 pc (C)
- LE.5263** Interchangeable self-sustaining gooseneck-type guide with a 420 nm high-power Violet-LED for NZ.9018, LE.5207 or LE.5212, 1 pc (D)
- LE.5264** Polarization filter, screw on type for Interchangeable self-sustaining gooseneck-type guides for NZ.9018, LE.5207 or LE.5212, 1 pc

● The LE.5212 in two different configurations

